

Part Numbering

[Part Number] DE1E3RA102MN4AN01F

DE1 | E3 | RA | 102 | M | N4 | A | N01F
 ① | ② | ③ | ④ | ⑤ | ⑥ | ⑦ | ⑧



① Series

Code	Series	Contents
DE1	Safety Standard Certified Lead Type Disc Ceramic Capacitors for Consumer Electronics & Industrial Equipment	IEC60384-14 ClassX1, Y1
DE2		IEC60384-14 ClassX1, Y2
DE6		IEC60384-14 ClassX1, Y2

② Temperature Characteristics

Code	Public STD Code	Cap. Change or Temp. Coeff.	Temperature Range
1X	SL	+350 to -1000ppm/°C	+20 to +85°C
B3	B	±10%	-25 to +85°C
E3	E	+20%, -55%	
F3	F	+30%, -80%	

③ Rated Voltage/Certified Type

Code	③ Individual Specification Code	Rated Voltage	Certified Type
KJ	E***	X1 : 440Vac(r.m.s.), Y2 : 300Vac(r.m.s.), 1000Vdc	Type KJ
	-		
KX	C***	X1 : 440Vac(r.m.s.), Y1 : 250Vac(r.m.s.)	Type KX
	N***	X1 : 440Vac(r.m.s.), Y1 : 250Vac(r.m.s.)	
	P***	X1 : 440Vac(r.m.s.), Y1 : 300Vac(r.m.s.)	
KY	M***	X1 : 250Vac(r.m.s.), Y2 : 250Vac(r.m.s.)	Type KY
RA	H***	X1 : 440Vac(r.m.s.)/1500Vdc, Y1 : 400Vac(r.m.s.)/1500Vdc	Type RA
	N***	X1 : 440Vac(r.m.s.)/1500Vdc, Y1 : 250Vac(r.m.s.)/1500Vdc	
	P***	X1 : 440Vac(r.m.s.)/1500Vdc, Y1 : 300Vac(r.m.s.)/1500Vdc	
	Q***	X1 : 500Vac(r.m.s.)/1500Vdc, Y1 : 500Vac(r.m.s.)/1500Vdc	
RB	R***	X1 : 760Vac(r.m.s.), Y1 : 500Vac(r.m.s.), 1500Vdc	Type RB
SA	T***	X1 : 300Vac(r.m.s.)/1500Vdc, Y2 : 250Vac(r.m.s.)/1500Vdc	Type SA
	X***	X1 : 300Vac(r.m.s.)/1500Vdc, Y2 : 300Vac(r.m.s.)/1500Vdc	
	Y***	X1 : 440Vac(r.m.s.)/1500Vdc, Y2 : 400Vac(r.m.s.)/1500Vdc	

Part Numbering

【Part Number】 DE1E3RA102MN4AN01F

DE1 | E3 | RA | 102 | M | N4 | A | N01F
 ① | ② | ③ | ④ | ⑤ | ⑥ | ⑦ | ⑧



④ Capacitance

Expressed by three figures. The unit is pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two numbers.

⑤ Capacitance Tolerance

Code	Capacitance Tolerance
J	±5%
K	±10%
M	±20%

⑥ Lead Style

Code	Lead Style	Dimensions		
		Lead Spacing	Lead Diameter	Pitch of Components
A2	Vertical Crimp Long	5mm	ø0.6 ± 0.05mm	—
A3		7.5mm		
A4		10mm		
B2/J2	Vertical Crimp Short	5mm	ø0.6 ± 0.05mm	—
B3/J3		7.5mm		
B4/J4		10mm		
N2	Vertical Crimp Taping	5mm	ø0.6 ± 0.05mm	12.7mm
N3		7.5mm		15mm
N4		10mm		25.4mm

⑦ Packaging

Code	Packaging
A	Ammo Pack Taping
B	Bulk

⑧ Individual Specification Code

For part number that cannot be identified without "Individual Specification," it is added at the end of part number, expressed by three or four-digit alphanumerics.