

# Type 2JM Wi-Fi™ Module

Qualcomm QCC730 Chipset for 802.11a/b/g/n  
Datasheet - Rev. 3

- Design Name: Type 2JM
- P/N: LBWA0ZZ2JM-001



## Table of Contents

|  |    |
|--|----|
| 1 Scope .....  | 5  |
| 2 Key Features .....   | 5  |
| 3 Ordering Information .....                                       | 5  |
| 4 Block Diagram .....  | 6  |
| 5 Certification Information .....                                  | 7  |
| 5.1 Radio Certification.....                                       | 7  |
| 5.2 Radio Regulatory Certification by Country.....                 | 8  |
| 6 Dimensions, Markings and Terminal Configurations .....           | 9  |
| 7 Module Pin Descriptions .....                                    | 10 |
| 7.1 Pin Assignments .....  | 10 |
| 7.2 Pin Descriptions .....   | 12 |
| 7.3 Configuration pins .....                                       | 13 |
| 7.4 Pin State .....  | 14 |
| 7.5 I/O Pin Mux Table .....  | 14 |
| 8 Absolute Maximum Ratings .....                                   | 15 |
| 9 Operating Conditions .....                                       | 15 |
| 9.1 Operating Conditions .....                                     | 15 |
| 9.2 Digital I/O Requirements .....                                 | 16 |
| 9.3 Sleep clock conditions.....                                    | 17 |
| 9.4 Power modes .....  | 18 |
| 9.5 Package Thermal Conditions .....                               | 19 |
| 10 Power Sequence .....  | 20 |
| 11 DC / RF Characteristics .....                                   | 21 |
| 11.1 DC/RF Characteristics for IEEE 802.11b - 2.4 GHz.....         | 21 |
| 11.1.1 High-Rate Condition for IEEE 802.11b - 2.4 GHz .....        | 21 |
| 11.1.2 Low-Rate Condition for IEEE 802.11b - 2.4 GHz .....         | 22 |
| 11.2 DC/RF Characteristics for IEEE 802.11g - 2.4 GHz.....         | 23 |
| 11.2.1 High-Rate Condition for IEEE 802.11g - 2.4 GHz .....        | 23 |
| 11.2.2 Low-Rate Condition for IEEE 802.11g - 2.4 GHz .....         | 24 |
| 11.3 DC/RF Characteristics for IEEE 802.11n (HT20) - 2.4 GHz.....  | 25 |
| 11.3.1 High-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz ..... | 25 |
| 11.3.2 Low-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz .....  | 26 |
| 11.4 DC/RF Characteristics for IEEE 802.11a - 5 GHz.....           | 27 |
| 11.4.1 High-Rate Condition for IEEE 802.11a - 5 GHz .....          | 27 |
| 11.4.2 Low-Rate Condition for IEEE 802.11a - 5 GHz .....           | 28 |

|  |    |
|--|----|
| 11.5 DC/RF Characteristics for IEEE 802.11n (HT20) - 5 GHz.....  | 29 |
| 11.5.1 High-Rate Condition for IEEE 802.11n (HT20) - 5 GHz ..... | 29 |
| 11.5.2 Low-Rate Condition for IEEE 802.11n (HT20) - 5 GHz.....   | 30 |
| 12 Land Pattern .....  | 31 |
| 13 Tape and Reel Packing.....                                    | 32 |
| 13.1 Dimensions of Tape (Plastic Tape).....                      | 32 |
| 13.2 Dimension of Reel.....                                      | 33 |
| 13.3 Taping Diagrams.....  | 34 |
| 13.4 Leader and Tail Tape .....                                  | 35 |
| 13.5 Packaging (Humidity Proof Packing) .....                    | 36 |
| 14 Notice .....  | 37 |
| 14.1 Storage Conditions.....                                     | 37 |
| 14.2 Handling Conditions .....                                   | 37 |
| 14.3 Standard PCB Design (Land Pattern and Dimensions) .....     | 37 |
| 14.4 Notice for Chip Placer .....                                | 38 |
| 14.5 Soldering Conditions .....                                  | 38 |
| 14.6 Cleaning.....   | 38 |
| 14.7 Operational Environment Conditions .....                    | 39 |
| 15 Preconditions to Use Our Products .....                       | 40 |
| Revision History.....  | 42 |

## Figures

|  |    |
|--|----|
| Figure 1: Block Diagram .....                                    | 6  |
| Figure 2: Dimensions, Markings and Terminal Configurations ..... | 9  |
| Figure 3: Structure .....  | 10 |
| Figure 4: Pin Assignments Bottom View .....                      | 10 |
| Figure 5: External 32.768 kHz sleep clock timing.....            | 17 |
| Figure 6: Package Thermal Conditions .....                       | 19 |
| Figure 7: Power on and Power off Sequence.....                   | 20 |
| Figure 8: Land Pattern (TOP VIEW).....                           | 31 |
| Figure 9: Dimensions of Tape (Unit: mm).....                     | 32 |
| Figure 10: Dimensions of Reel (Unit: mm) .....                   | 33 |
| Figure 11: Taping Diagrams.....                                  | 34 |
| Figure 12: Taping Diagrams (Close Up).....                       | 34 |
| Figure 13: Leader and Tail Tape.....                             | 35 |
| Figure 14: Peeling Force.....                                    | 35 |
| Figure 15: Humidity Proof Packaging.....                         | 36 |

|  |    |
|--|----|
| Figure 16: Reflow Soldering Standard Conditions (Example)..... | 38 |
|--|----|

## Tables

|   |    |
|---|----|
| Table 1: Document Conventions.....  | 4  |
| Table 2: Ordering Information.....  | 5  |
| Table 3: Transmit Power Limit Files.....                                  | 7  |
| Table 4: Markings.....  | 9  |
| Table 5: Dimensions.....  | 9  |
| Table 6: Terminal Configurations.....                                     | 11 |
| Table 7: Pin Descriptions.....  | 12 |
| Table 8: Conditions of bootstrap configuration pins.....                  | 13 |
| Table 9: GPIO pull state setting for difference GPIO for UART option..... | 14 |
| Table 10: GPIO Mux Table.....   | 14 |
| Table 11: Absolute Maximum Ratings.....                                   | 15 |
| Table 12: Operating Conditions.....                                       | 15 |
| Table 13: Digital I/O Requirements Parameters (3.3V I/O operation).....   | 16 |
| Table 14: Digital I/O Requirements Parameters (1.8V I/O operation).....   | 16 |
| Table 15: External Sleep Clock Requirements Parameters.....               | 17 |
| Table 16: Sleep modes.....  | 18 |
| Table 17: Characteristics Values for IEEE 802.11b - 2.4 GHz.....          | 21 |
| Table 18: High-Rate Condition for IEEE 802.11b - 2.4 GHz.....             | 21 |
| Table 19: Low-Rate Condition for IEEE 802.11b - 2.4 GHz.....              | 22 |
| Table 20: Characteristics Values for IEEE 802.11g - 2.4 GHz.....          | 23 |
| Table 21: High-Rate Condition for IEEE 802.11g - 2.4 GHz.....             | 23 |
| Table 22: Low-Rate Condition for IEEE 802.11g - 2.4 GHz.....              | 24 |
| Table 23: Characteristics Values for IEEE 802.11n (HT20) - 2.4 GHz.....   | 25 |
| Table 24: High-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz.....      | 25 |
| Table 25: Low-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz.....       | 26 |
| Table 26: Characteristics Values for IEEE 802.11a - 5 GHz.....            | 27 |
| Table 27: High-Rate Condition for IEEE 802.11a - 5 GHz.....               | 27 |
| Table 28: Low-Rate Condition for IEEE 802.11a - 5 GHz.....                | 28 |
| Table 29: Characteristics Values for IEEE 802.11n (HT20) - 5 GHz.....     | 29 |
| Table 30: High-Rate Condition for IEEE 802.11n (HT20) - 5 GHz.....        | 29 |
| Table 31: Low-Rate Condition for IEEE 802.11n (HT20) - 5 GHz.....         | 30 |
| Table 32: Taping Specifications.....                                      | 34 |

## About This Document

Murata's Type 2JM is a small and ultra-low power consumption module based on Qualcomm's QCC730 WiFi chipset, supporting IEEE 802.11a/b/g/n (up to MCS3). This datasheet describes Type 2JM module in detail.



Please be aware that an important notice concerning availability, standard warranty and use in critical applications of Murata products and disclaimers thereto appears at the end of this specification sheet.









## Audience & Purpose

Intended audience includes any customer looking to integrate this module into their product. In particular, RF, hardware, software, and systems engineers.

## Document Conventions

**Table 1** describes the document conventions.

**Table 1: Document Conventions**

| Conventions   | Description   |
|---|---|
|  | <b>Warning Note</b><br>Indicates very important note. Users are strongly recommended to review.   |
|  | <b>Info Note</b><br>Intended for informational purposes. Users should review.   |
|  | <b>Menu Reference</b><br>Indicates menu navigation instructions.<br><b>Example:</b> Insert → Tables → Quick Tables → Save Selection to Gallery   |
|  | <b>External Hyperlink</b><br>This symbol indicates a hyperlink to an external document or website.<br><b>Example:</b> <a href="#">Murata Manufacturing Co., Ltd.</a> <br>Click on the text to open the external link.  |
|  | <b>Internal Hyperlink</b><br>This symbol indicates a hyperlink within the document.<br><b>Example:</b> <a href="#">Scope</a> <br>Click on the text to open the link.   |
| <code>Console input/output or code snippet</code>                                   | <b>Console I/O or Code Snippet</b><br>This text <b>Style</b> denotes console input/output or a code snippet.  |
| <code># Console I/O comment<br/>// Code snippet comment</code>                      | <b>Console I/O or Code Snippet Comment</b><br>This text <b>Style</b> denotes a console input/output or code snippet comment. <ul style="list-style-type: none"> <li>• Console I/O comment (preceded by "#") is for informational purposes only and does not denote actual console input/output.</li> <li>• Code Snippet comment (preceded by "//") may exist in the original code.</li> </ul> |

## 1 Scope

This specification characterizes the IEEE 802.11a/b/g/n WiFi module.

## 2 Key Features

- ◆ Qualcomm QCC730 micropower WiFi chip inside
- ◆ Supports IEEE 802.11a/b/g/n specification: Dual band 2.4 GHz and 5 GHz
- ◆ SISO with 20 MHz channels
- ◆ Up to MCS3 data rates
- ◆ On chip Microcontroller and Memory (Cortex-M4 60MHz, 1.5MB RRAM, 640KB SRAM)
- ◆ Support external flash memory to extend user programable memory area and XiP boot.
- ◆ Interface: 1x SPI(Peripheral),1x QSPI(Controller),1x I2C(Controller),UART (2-wire),15x GPIO
- ◆ Temperature Range: -20 °C to 85 °C
- ◆ Dimensions: 8.47 x 8.1 x 2.35 mm
- ◆ Weight: 231 mg
- ◆ MSL: 3
- ◆ Surface-mount type
- ◆ RoHS compliant
- ◆ Total FIT: 71.4

## 3 Ordering Information

**Table 2** provides the ordering information for Type 2JM module.


**Table 2: Ordering Information**

| Ordering Part Number | Description                        |
|----------------------|------------------------------------|
| LBWA0ZZ2JM-001       | Type2JM Module Mass Production P/N |
| LBWA0ZZ2JM-SMP       | Type2JM Module Sample P/N          |
| LBWA0ZZ2JM-EVB       | Type2JM Evaluation Board P/N       |

## 4 Block Diagram

Figure 1 shows the block diagram of Type 2JM module.

Figure 1: Block Diagram




## 5 Certification Information

This section has information about radio certification.

### 5.1 Radio Certification

Transmit output power setting and Country output power setting is written in OTP and BDF field. Please do not overwrite OTP and BDF area. See below memory map. Regulatory/Country transmit power configuration files to leverage Murata's regulatory Certification are provided at [GitHub murata-wireless](#).

**Table 3: Transmit Power Limit Files**

| Country                        | ID   | Country Code |     | Remarks                 |
|--------------------------------|--|--------------|-----|-------------------------|
| USA (FCC)                      | FCC 15.247, 15.407<br>VPYLBWA0ZZ2JM  | US           | 840 |                         |
| Canada (IC)                    | RSS-247<br>772C-LBWA0ZZ2JM   | CA           | 124 |                         |
| Europe                         | EN300328, EN301893   | DE           | 276 | Conducted test report   |
| Japan                          | Japanese type<br>certification is prepared.<br>R 003-250368  | JP           | 392 |                         |
| Taiwan (NCC)                   | LP0002<br> CCAM26Y20010T1 | TW           | 158 | Need Host certification |
| Australia/New Zealand<br>(RCM) | AS/NZS 4268:2017   | AU           | 36  | Conducted test report   |
|                                |  | NZ           | 554 |                         |

#### RRAM Memory map

|                  |     |          |
|------------------|-----|----------|
| <b>OTP</b>       | 4K  | 0x1A0000 |
| <b>Reserved</b>  |     | 0x1A1000 |
| <b>PBL</b>       | 32K | 0x200000 |
| <b>FDT</b>       | 1K  | 0x208000 |
| <b>PBL patch</b> | 8K  | 0x208400 |
| <b>SBLA</b>      | 32K | 0x20A400 |
| <b>SBLB</b>      | 32K | 0x212400 |
| <b>APP</b>       |     | 0x21A400 |
| <b>BDF</b>       | 24K | 0x37A000 |

## 5.2 Radio Regulatory Certification by Country

Murata have prepared the document about Radio Regulatory Certification separately.

This document is designed to ensure that module manufacturers correctly communicate the necessary information to host manufacturers that incorporate their modules.

Refer to [Regulatory Information]: [Type 2JM Radio Law Approval Application Note](#) for Radio Law Certification user manual.




If you don't follow the rule written in Type 2JM Radio Law Approval Application Note, there is a risk of conflict Radio Law Certification.  
Please be sure to check the documents.

## 6 Dimensions, Markings and Terminal Configurations

This section has information on dimensions, markings, and terminal configurations.

**Figure 2: Dimensions, Markings and Terminal Configurations**



**Table 4: Markings**

| Marking | Meaning        |
|---------|----------------|
| A       | Module Type    |
| B       | 2D Code        |
| C       | Murata Logo    |
| D       | Pin1 indicator |

**Table 5: Dimensions**


| Marks | Dimensions      | Marks | Dimensions     | Marks | Dimensions    |
|-------|-----------------|-------|----------------|-------|---------------|
| Lm    | $8.47 \pm 0.2$  | W     | $8.1 \pm 0.2$  | T     | 2.35mm MAX    |
| a1    | $0.6 \pm 0.1$   | a2    | $0.3 \pm 0.1$  | a3    | $1.0 \pm 0.1$ |
| b1    | $0.625 \pm 0.1$ | b2    | $0.25 \pm 0.1$ | b3    | $0.2 \pm 0.1$ |
| b4    | $2.0 \pm 0.1$   | b5    | $2.1 \pm 0.1$  | b6    | $2.0 \pm 0.1$ |
| c1    | $0.6 \pm 0.1$   | c2    | $0.3 \pm 0.1$  | c3    | $1.0 \pm 0.1$ |
| e1    | $0.535 \pm 0.1$ | e2    | $0.25 \pm 0.1$ | e3    | $0.2 \pm 0.1$ |
| e4    | $2.5 \pm 0.1$   | e5    | $2.0 \pm 0.1$  |       |               |
| m1    | $0.4 \pm 0.1$   | m2    | $0.4 \pm 0.1$  |       |               |



T dimension does not include height of solder bumps.  
Unit of Dimensions are in mm.

**Figure 3** shows the structure of Type 2JM.

**Figure 3: Structure**




## 7 Module Pin Descriptions

This section has the pin descriptions of Type 2JM and pin assignments layout descriptions.

### 7.1 Pin Assignments

The pin assignment (Bottom View) layout is shown in **Figure 4**.

**Figure 4: Pin Assignments Bottom View**



**Table 6** illustrates the terminal configurations.

**Table 6: Terminal Configurations**

| No. | Terminal Name     | No. | Terminal Name | No. | Terminal Name |
|-----|-------------------|-----|---------------|-----|---------------|
| 1   | GPIO_11           | 18  | JTAG_TDI      | 35  | GND           |
| 2   | GPIO_4            | 19  | JTAG_TMS      | 36  | GND           |
| 3   | GPIO_6            | 20  | JTAG_TRST_N   | 37  | GND           |
| 4   | GPIO_5            | 21  | JTAG_TDO      | 38  | 1V8           |
| 5   | GPIO_3            | 22  | JTAG_TCK      | 39  | GND           |
| 6   | GPIO_2            | 23  | GND           | 40  | GPIO_14       |
| 7   | GPIO_1            | 24  | GND           | 41  | GPIO_13       |
| 8   | GPIO_0            | 25  | GND           | 42  | GND           |
| 9   | EXT_WAKEUP_INTR_N | 26  | GND           | 43  | GPIO_8        |
| 10  | CHIP_ON           | 27  | GND           | 44  | GPIO_7        |
| 11  | GND               | 28  | RFIO          | 45  | GPIO_12       |
| 12  | VBAT              | 29  | GND           | 46  | GND           |
| 13  | GND               | 30  | GND           | 47  | GND           |
| 14  | VIO               | 31  | GND           | 48  | GND           |
| 15  | GND               | 32  | GND           | 49  | GND           |
| 16  | GPIO_10           | 33  | GND           | 50  | GND           |
| 17  | GPIO_9            | 34  | GND           |     |               |

## 7.2 Pin Descriptions

**Table 7** shows the pin description for Type 2JM modules.

**Table 7: Pin Descriptions**

| No. | Pin name          | I/O Type | Internal PU/PD |        | Power source | Descriptions  |
|-----|-------------------|----------|----------------|--------|--------------|---|
|     |                   |          | Reset          | Active |              |   |
| 1   | GPIO_11           | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10. Option: XIP Flash ROM interface.   |
| 2   | GPIO_4            | DIO      | PD             | NP     | VIO          | General purpose I/O. See Table 10. Option: XIP Flash ROM interface.   |
| 3   | GPIO_6            | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10. Option: XIP Flash ROM interface.   |
| 4   | GPIO_5            | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10. Option: XIP Flash ROM interface.   |
| 5   | GPIO_3            | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10. Bootstrap option pin. Set 1 during booting-up by internal 10k ohm pull-up for IoT mode. See section 7.3. |
| 6   | GPIO_2            | DIO      | PU             | NP     | VIO          | General purpose I/O. See Table 10. Bootstrap option pin. Do not drive during booting-up with IoT mode.                                      |
| 7   | GPIO_1            | DIO      | PU             | NP     | VIO          | General purpose I/O. See Table 10. Bootstrap option pin. Do not drive during booting-up with IoT mode.                                      |
| 8   | GPIO_0            | DIO      | PD             | NP     | VIO          | General purpose I/O. See Table 10.  |
| 9   | EXT_WAKEUP_INTR_N | DI       | PU             | PU     | VIO          | External wakeup input   |
| 10  | CHIP_ON           | DI       | -              | -      |              | Chip power on. Can be Open. This terminal has internal RC delay circuit.  |
| 11  | GND               | GND      | -              | -      | -            | Ground  |
| 12  | VBAT              | PWR      | -              | -      | VBAT         | VBAT power supply   |
| 13  | GND               | GND      | -              | -      | -            | Ground  |
| 14  | VIO               | PWR      | -              | -      | VIO          | VIO power supply  |
| 15  | GND               | GND      | -              | -      | -            | Ground  |
| 16  | GPIO_10           | DIO      | PD             | NP     | VIO          | General purpose I/O. See Table 10.  |
| 17  | GPIO_9            | DIO      | PD             | NP     | VIO          | General purpose I/O. See Table 10.  |
| 18  | JTAG_TDI          | DI       | PU             | PU     | VIO          | JTAG signal   |
| 19  | JTAG_TMS          | DI       | PU             | PU     | VIO          | JTAG signal   |
| 20  | JTAG_TRST_N       | DI       | PU             | PU     | VIO          | JTAG signal   |
| 21  | JTAG_TDO          | DO       | PD             | PD     | VIO          | JTAG signal   |
| 22  | JTAG_TCK          | DI       | PD             | PD     | VIO          | JTAG signal   |
| 23  | GND               | GND      | -              | -      | -            | Ground  |
| 24  | GND               | GND      | -              | -      | -            | Ground  |
| 25  | GND               | GND      | -              | -      | -            | Ground  |
| 26  | GND               | GND      | -              | -      | -            | Ground  |
| 27  | GND               | GND      | -              | -      | -            | Ground  |
| 28  | RFIO              | GND      | -              | -      | -            | Ground  |
| 29  | GND               | GND      | -              | -      | -            | Ground  |
| 30  | GND               | GND      | -              | -      | -            | Ground  |
| 31  | GND               | GND      | -              | -      | -            | Ground  |
| 32  | GND               | GND      | -              | -      | -            | Ground  |
| 33  | GND               | GND      | -              | -      | -            | Ground  |
| 34  | GND               | GND      | -              | -      | -            | Ground  |

| No. | Pin name | I/O Type | Internal PU/PD |        | Power source | Descriptions  |
|-----|----------|----------|----------------|--------|--------------|---|
|     |          |          | Reset          | Active |              |   |
| 35  | GND      | GND      | -              | -      | -            | Ground  |
| 36  | GND      | GND      | -              | -      | -            | Ground  |
| 37  | GND      | GND      | -              | -      | -            | Ground  |
| 38  | 1V8      | GND      | -              | -      | -            | Ground  |
| 39  | GND      | GND      | -              | -      | -            | Ground  |
| 40  | GPIO_14  | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10.  |
| 41  | GPIO_13  | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10.  |
| 42  | GND      | GND      | -              | -      | -            | Ground  |
| 43  | GPIO_8   | DIO      | PU             | PU     | VIO          | General purpose I/O. See Table 10.<br>Default: SPI Interrupt. Send approx. 2 usec pulse to the host once RX data is sent over to the host.<br>Option: 32kHz Sleep clock in for more accurate sleep management than module internal sleep clock. |
| 44  | GPIO_7   | DIO      | PD             | PD     | VIO          | General purpose I/O. See Table 10.<br>Option: XIP Flash ROM interface.  |
| 45  | GPIO_12  | DIO      | PU             | PU     | VIO          | General purpose I/O. See Table 10.<br>Option: XIP Flash ROM interface.  |
| 46  | GND      | GND      | -              | -      | -            | Ground  |
| 47  | GND      | GND      | -              | -      | -            | Ground  |
| 48  | GND      | GND      | -              | -      | -            | Ground  |
| 49  | GND      | GND      | -              | -      | -            | Ground  |
| 50  | GND      | GND      | -              | -      | -            | Ground  |

## 7.3 Configuration pins

**Table 8** shows bootstrap configuration for Type 2JM modules.

**Table 8: Conditions of bootstrap configuration pins**

| GPIO_1 | GPIO_2 | GPIO_3 | mode     | Descriptions   |
|--------|--------|--------|----------|--|
| NA     | NA     | 1      | IoT mode | GPIO_3 is internally PU by 10k ohm. Do not driver GPIO_1 and GPIO_2 during booting up. |
| Others | Others | Others | Reserved |  |

## 7.4 Pin State

**Table 9** shows GPIO pull state for UART option of Type 2JM module.

**Table 9: GPIO pull state setting for difference GPIO for UART option**

| GPIO    | Type | Reset | UART option 1<br>(GPIO 11/12)<br>Reset | UART option 2<br>(GPIO 13/14)<br>Reset | UART option 3<br>(GPIO 9/10)<br>Reset | UART option 4<br>(GPIO 1/3)<br>Reset |
|---------|------|-------|--|--|---------------------------------------|--------------------------------------|
| GPIO_0  | DIO  | PD    | NP                                     | NP                                     | NP                                    | NP                                   |
| GPIO_1  | DIO  | PU    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_2  | DIO  | PU    | NP                                     | NP                                     | NP                                    | NP                                   |
| GPIO_3  | DIO  | PD    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_4  | DIO  | PD    | PD                                     | PD                                     | PD                                    | PD                                   |
| GPIO_5  | DIO  | PD    | NP                                     | PD                                     | PD                                    | PD                                   |
| GPIO_6  | DIO  | PD    | PD                                     | PD                                     | PD                                    | PD                                   |
| GPIO_7  | DIO  | PD    | PD                                     | PD                                     | PD                                    | PD                                   |
| GPIO_8  | DIO  | PU    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_9  | DIO  | PD    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_10 | DIO  | PD    | PD                                     | PD                                     | PU                                    | PD                                   |
| GPIO_11 | DIO  | PD    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_12 | DIO  | PU    | PU                                     | PD                                     | PD                                    | PD                                   |
| GPIO_13 | DIO  | PD    | PU                                     | PU                                     | PU                                    | PU                                   |
| GPIO_14 | DIO  | PD    | PD                                     | PU                                     | PD                                    | PD                                   |

## 7.5 I/O Pin Mux Table

**Table 10** shows the pin description for Type 2JM modules.

**Table 10: GPIO Mux Table**

| GPIO            | QSPI     | SPI      | I2C | UART    | BT          | PTA         | 32kHz<br>Sleep Clock |
|-----------------|----------|----------|-----|---------|-------------|-------------|----------------------|
| GPIO_0          |          | SPI_CLK  |     |         |             |             |                      |
| GPIO_1          |          | SPI_CS#  |     | UART_RX |             |             |                      |
| GPIO_2          |          | SPI_MOSI |     |         |             |             |                      |
| GPIO_3          |          | SPI_MISO |     | UART_TX |             |             |                      |
| GPIO_4          | QSPI_CLK |          |     |         |             |             |                      |
| GPIO_5<br>(AON) | QSPI_CS# |          |     |         |             |             |                      |
| GPIO_6          | QSPI_D0  |          |     |         |             |             |                      |
| GPIO_7          | QSPI_D1  |          |     |         |             |             |                      |
| GPIO_8          |          | SPI_INT  |     |         |             | BT PRIORITY | 32k IN               |
| GPIO_9<br>(AON) |          |          | SDA | UART_TX |             |             |                      |
| GPIO_10         |          |          | SCL | UART_RX |             |             |                      |
| GPIO_11         | QSPI_D2  |          |     | UART_TX |             |             |                      |
| GPIO_12         | QSPI_D3  |          |     | UART_RX |             |             |                      |
| GPIO_13         |          |          |     | UART_TX | WSI_CLK_BT  | BT_ACTIVE   |                      |
| GPIO_14         |          |          |     | UART_RX | WSI_DATA_BT | WL_ACTIVE   |                      |

## 8 Absolute Maximum Ratings

The absolute maximum ratings are shown in **Table 11**.

**Table 11: Absolute Maximum Ratings**

| Parameter                | Minimum | Maximum | Unit |   |
|--------------------------|---------|---------|------|---|
| Storage Temperature      | -40     | 85      | °C   |   |
| Supply Voltage           | VBAT    | -0.3    | 4.0  | V |
|                          | 1V8     | -0.3    | 1.98 | V |
|                          | VIO     |         | 3.6  | V |
| Maximum RF input at RFIO |         | 10      | dBm  |   |



Stresses in excess of the absolute ratings may cause permanent damage. Functional operation is not implied under these conditions. Exposure to absolute ratings for extended periods of time may adversely affect reliability. No damage assuming only one parameter is set at limit at a time with all other parameters are set within operating condition.

## 9 Operating Conditions

### 9.1 Operating Conditions

The operating conditions are shown in **Table 12**.

**Table 12: Operating Conditions**

| Parameter             |            | Minimum | Typical | Maximum | Unit |
|-----------------------|------------|---------|---------|---------|------|
| Operating Temperature | Ta         | -20     | 25      | +85     | °C   |
|                       | Tj         | -       | -       | +125    | °C   |
| Supply Voltage        | VBAT       | 2.6     | 3.3     | 3.6     | V    |
|                       | 1V8        | 1.71    | 1.8     | 1.89    | V    |
|                       | VIO (1.8V) | -0.3    | 1.8     | 2.1     | V    |
|                       | VIO (3.3V) | -0.3    | 3.3     | 3.6     | V    |



- Operation beyond the recommended operating conditions is neither recommended nor guaranteed.

## 9.2 Digital I/O Requirements

**Table 13** and **Table 14** shows the digital I/O requirements.

**Table 13: Digital I/O Requirements Parameters (3.3V I/O operation)**

| Parameter       | Description               | Condition | Minimum | Typical | Maximum | Unit |
|-----------------|---------------------------|-----------|---------|---------|---------|------|
| V <sub>IH</sub> | High-level input voltage  | -         | 2.40    | –       | 3.6     | V    |
| V <sub>IL</sub> | Low-level input voltage   | -         | -0.3    | –       | 0.8     | V    |
| V <sub>OH</sub> | High-level output voltage | -         | 2.4     | –       | 3.6     | V    |
| V <sub>OL</sub> | Low-level output voltage  | -         | –       | –       | 0.4     | V    |
| I <sub>IH</sub> | High-level input current  | Rpd: ON   | –       | –       | 10      | μA   |
|                 |                           | Rpd: OFF  | –       | –       | 0.1     | μA   |
| I <sub>IL</sub> | Low-level input current   | Rpd: ON   | –       | –       | 10      | μA   |
|                 |                           | Rpd: OFF  | –       | –       | 0.1     | μA   |


**Table 14: Digital I/O Requirements Parameters (1.8V I/O operation)**

| Parameter       | Description               | Condition | Minimum | Typical | Maximum | Unit |
|-----------------|---------------------------|-----------|---------|---------|---------|------|
| V <sub>IH</sub> | High-level input voltage  | -         | 1.17    | –       | 2.1     | V    |
| V <sub>IL</sub> | Low-level input voltage   | -         | -0.3    | –       | 0.63    | V    |
| V <sub>OH</sub> | High-level output voltage | -         | 1.35    | –       | –       | V    |
| V <sub>OL</sub> | Low-level output voltage  | -         | –       | –       | 0.45    | V    |
| I <sub>IH</sub> | High-level input current  | Rpd: ON   | –       | –       | 10      | μA   |
|                 |                           | Rpd: OFF  | –       | –       | 0.1     | μA   |
| I <sub>IL</sub> | Low-level input current   | Rpd: ON   | –       | –       | 10      | μA   |
|                 |                           | Rpd: OFF  | –       | –       | 0.1     | μA   |

### 9.3 Sleep clock conditions

**Figure 5** and **Table 15** shows the requirements of external sleep clock. This external clock is optional because QCC730 chipset has internal RTC.

**Figure 5: External 32.768 kHz sleep clock timing**



**Table 15: External Sleep Clock Requirements Parameters**

| Parameter | Description                    | Min         | Typ    | Max   | Unit |
|-----------|--------------------------------|-------------|--------|-------|------|
| CK1       | Clock rate                     | –           | 32.768 | –     | kHz  |
| CK2       | Fall time                      | 1           | –      | 100   | ns   |
| CK3       | Rise time                      | 1           | –      | 100   | ns   |
| CK4       | Duty cycle (high to low ratio) | 15          | –      | 85    | %    |
| CK5       | Frequency stability            | -200        | –      | 200   | PPM  |
| CK6       | Input high voltage             | $0.8 * VIO$ | –      | $VIO$ | V    |
| CK7       | Input low voltage              | -0.3        | –      | $VIO$ | V    |



Power up VIO before the external sleep clock is required.

## 9.4 Power modes

**Table 15** shows internal state in each sleep mode.

**Table 16: Sleep modes**

| Power Mode       | CPU | Memory   | RTC | Wakeup Source                  | Description   | Use Case          |
|------------------|-----|----------|-----|--------------------------------|---|-------------------|
| Active           | On  | On       | On  | N/A                            | Normal operation  | Awake             |
| Sleep            | Off | Retained | Off | DTIM timer                     | <ul style="list-style-type: none"> <li>• Enter When RTOS is idle, and WLAN is connected*</li> <li>• Maintain WLAN connection</li> <li>• When awake, continue to run from sleep point</li> </ul> | WLAN DTIM         |
| Deep Sleep       | Off | Off      | Off | RTC timer or EXT_WAKEUP_INTR_N | <ul style="list-style-type: none"> <li>• Enter when RTOS is idle, and WLAN is disconnected*</li> <li>• Nothing maintained</li> <li>• When awake, restart from PBL</li> </ul>                    | Alarm or Shutdown |
| Indefinite Sleep | Off | Off      | Off | EXT_WAKEUP_INTR_N              | Same as Deep Sleep, except not waked up by RTC timer  | Shutdown          |



Actual entering condition is complicated, such as considering sleep interval.


## 9.5 Package Thermal Conditions

- $R\psi_{jt}$  : 12.845 °C/W
- $R\psi_{jt} = (T_j - T_t)/P$



$T_j$ : Junction temperature (°C),  $T_t$ : Top temperature (°C),  $P$ : Total Power Consumption (W)

**Figure 6: Package Thermal Conditions**




## 10 Power Sequence

This section describes the power-on and power-off sequences along with their parameters.

**Figure 7** shows the Power on sequence. The CHIP\_ON is the chip power on pin and all supplies should be stable for a minimum of 1.8 ms before CHIP\_ON is asserted (that is. Is greater than  $V_{IL}$  for VIO).

**Figure 7: Power on and Power off Sequence**



CHIP\_ON should be open. CHIP\_ON is generated by VBAT+RC delay in Host-less mode.

## 11 DC / RF Characteristics

### 11.1 DC/RF Characteristics for IEEE 802.11b - 2.4 GHz

Table 17: Characteristics Values for IEEE 802.11b - 2.4 GHz

| Items             | Contents           |
|-------------------|--------------------|
| Specification     | IEEE 802.11b       |
| Mode              | DSSS / CCK         |
| Channel Frequency | 2412 to 2472 MHz   |
| Data Rate         | 1, 2, 5.5, 11 Mbps |



Short preamble is not supported in 1, 2, 5.5 Mbps mode. Please do not set "4", "5" and "6" if fixed data rate mode is used by SetRate command.

#### 11.1.1 High-Rate Condition for IEEE 802.11b - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 7.5 dBm at module pad, 11 Mbps mode

Table 18: High-Rate Condition for IEEE 802.11b - 2.4 GHz

| Items                           | Contents |                |         |      |
|---------------------------------|----------|----------------|---------|------|
| DC Characteristics              | Minimum  | Typical        | Maximum | Unit |
| DC Current                      |          |                |         |      |
| • Tx mode                       |          | 80             | 110     | mA   |
| • Rx mode                       |          | 6              | 18      | mA   |
| Tx Characteristics              | Minimum  | Target setting | Maximum | Unit |
| Output Power                    | 5.0      | 7.5            | 11.0    | dBm  |
| Spectrum Mask Margin            |          |                |         |      |
| • 1st side lobes                | 0        |                |         | dB   |
| • 2nd side lobes                | 0        |                |         | dB   |
| Power-on/off ramp               |          |                | 2.0     | μs   |
| RF Carrier Suppression          | 15       |                |         | dB   |
| Modulation Accuracy             |          |                | 35      | %    |
| Frequency Tolerance             | -20      |                | 20      | ppm  |
| Spurious Emissions              |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)    |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)    |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)  |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz) |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)  |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)  |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)  |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)  |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz) |          |                | -36     | dBm  |
| • 1000 - 12750 MHz (BW = 1 MHz) |          |                | -30     | dBm  |

| Items                                 | Contents |         |         |      |
|---------------------------------------|----------|---------|---------|------|
|                                       | Minimum  | Typical | Maximum | Unit |
| <b>Rx Characteristics</b>             |          |         |         |      |
| Minimum Input Level (FER ≤ 8%)        |          |         | -76     | dBm  |
| Maximum Input Level (FER ≤ 8%)        | -10      |         |         | dBm  |
| Adjacent Channel Rejection (FER < 8%) | 35       |         |         | dB   |

## 11.1.2 Low-Rate Condition for IEEE 802.11b - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 7.5 dBm at module pad, 1 Mbps mode

**Table 19: Low-Rate Condition for IEEE 802.11b - 2.4 GHz**

| Items                                 | Contents       |                       |                |             |
|---------------------------------------|----------------|-----------------------|----------------|-------------|
|                                       | Minimum        | Typical               | Maximum        | Unit        |
| <b>DC Characteristics</b>             |                |                       |                |             |
| DC Current                            |                |                       |                |             |
| • Tx mode                             |                | 80                    | 110            | mA          |
| • Rx mode                             |                | 6                     | 18             | mA          |
| <b>Tx Characteristics</b>             | <b>Minimum</b> | <b>Target setting</b> | <b>Maximum</b> | <b>Unit</b> |
| Output Power                          | 5.0            | 7.5                   | 11.0           | dBm         |
| Spectrum Mask Margin                  |                |                       |                |             |
| • 1st side lobes                      | 0              |                       |                | dB          |
| • 2nd side lobes                      | 0              |                       |                | dB          |
| Power-on/off ramp                     |                |                       | 2.0            | μs          |
| RF Carrier Suppression                | 15             |                       |                | dB          |
| Modulation Accuracy                   |                |                       | 35             | %           |
| Frequency Tolerance                   | -20            |                       | 20             | ppm         |
| Spurious Emissions                    |                |                       |                |             |
| • 30 - 47 MHz (BW = 100 kHz)          |                |                       | -36            | dBm         |
| • 47 - 74 MHz (BW = 100 kHz)          |                |                       | -54            | dBm         |
| • 74 - 87.5 MHz (BW = 100 kHz)        |                |                       | -36            | dBm         |
| • 87.5 - 118 MHz (BW = 100 kHz)       |                |                       | -54            | dBm         |
| • 118 - 174 MHz (BW = 100 kHz)        |                |                       | -36            | dBm         |
| • 174 - 230 MHz (BW = 100 kHz)        |                |                       | -54            | dBm         |
| • 230 - 470 MHz (BW = 100 kHz)        |                |                       | -36            | dBm         |
| • 470 - 862 MHz (BW = 100 kHz)        |                |                       | -54            | dBm         |
| • 862 - 1000 MHz (BW = 100 kHz)       |                |                       | -36            | dBm         |
| • 1000 - 12750 MHz (BW = 1 MHz)       |                |                       | -30            | dBm         |
| <b>Rx Characteristics</b>             | <b>Minimum</b> | <b>Typical</b>        | <b>Maximum</b> | <b>Unit</b> |
| Minimum Input Level (FER ≤ 8%)        |                |                       | -80            | dBm         |
| Maximum Input Level (FER ≤ 8%)        | -4             |                       |                | dBm         |
| Adjacent Channel Rejection (FER < 8%) | 35             |                       |                | dB          |

## 11.2 DC/RF Characteristics for IEEE 802.11g - 2.4 GHz

**Table 20: Characteristics Values for IEEE 802.11g - 2.4 GHz**

| Items             | Contents              |
|-------------------|-----------------------|
| Specification     | IEEE 802.11g          |
| Mode              | OFDM                  |
| Channel Frequency | 2412 to 2472 MHz      |
| Data Rate         | 6, 9, 12, 18, 24 Mbps |

### 11.2.1 High-Rate Condition for IEEE 802.11g - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 8.0 dBm at module pad, 24 Mbps mode

**Table 21: High-Rate Condition for IEEE 802.11g - 2.4 GHz**

| Items                                  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                     | Minimum  | Typical        | Maximum | Unit |
| DC Current                             |          |                |         |      |
| • Tx mode                              |          | 80             | 110     | mA   |
| • Rx mode                              |          | 6              | 18      | mA   |
| Tx Characteristics                     | Minimum  | Target setting | Maximum | Unit |
| Output Power                           | 6.0      | 8.0            | 10.0    | dBm  |
| Spectrum Mask Margin                   |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)        | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)     | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)     | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)           | 0        |                |         | dB   |
| Constellation Error (EVM)              |          |                | -16     | dB   |
| Frequency Tolerance                    | -20      |                | 20      | ppm  |
| Spurious Emissions                     |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)           |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)           |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)        |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)         |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)         |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)        |          |                | -36     | dBm  |
| • 1000 - 12750 MHz (BW = 1 MHz)        |          |                | -30     | dBm  |
| Rx Characteristics                     | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER < 10%)        |          |                | -74     | dBm  |
| Maximum Input Level (PER < 10%)        | -20      |                |         | dBm  |
| Adjacent Channel Rejection (PER < 10%) | 8        |                |         | dB   |

## 11.2.2 Low-Rate Condition for IEEE 802.11g - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 9.5 dBm at module pad, 6 Mbps mode

**Table 22: Low-Rate Condition for IEEE 802.11g - 2.4 GHz**

| Items                                  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                     | Minimum  | Typical        | Maximum | Unit |
| DC Current                             |          |                |         |      |
| • Tx mode                              |          | 80             | 110     | mA   |
| • Rx mode                              |          | 6              | 18      | mA   |
| Tx Characteristics                     | Minimum  | Target setting | Maximum | Unit |
| Output Power                           | 7.5      | 9.5            | 11.5    | dBm  |
| Spectrum Mask Margin                   |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)        | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)     | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)     | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)           | 0        |                |         | dB   |
| Constellation Error (EVM)              |          |                | -5      | dB   |
| Frequency Tolerance                    | -20      |                | 20      | ppm  |
| Spurious Emissions                     |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)           |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)           |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)        |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)         |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)         |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)         |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)        |          |                | -36     | dBm  |
| • 1000 - 12750 MHz (BW = 1 MHz)        |          |                | -30     | dBm  |
| Rx Characteristics                     | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER < 10%)        |          |                | -82     | dBm  |
| Maximum Input Level (PER < 10%)        | -20      |                |         | dBm  |
| Adjacent Channel Rejection (PER < 10%) | 16       |                |         | dB   |

## 11.3 DC/RF Characteristics for IEEE 802.11n (HT20) - 2.4 GHz

**Table 23: Characteristics Values for IEEE 802.11n (HT20) - 2.4 GHz**

| Items             | Contents               |
|-------------------|------------------------|
| Specification     | IEEE 802.11n 20 MHz BW |
| Mode              | OFDM                   |
| Channel Frequency | 2412 to 2472 MHz       |
| Data Rate         | MCS0-MCS3              |

### 11.3.1 High-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 8.0 dBm at module pad, MCS3 mode

**Table 24: High-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz**

| Items  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| DC Current   |          |                |         |      |
| • Tx mode  |          | 80             | 110     | mA   |
| • Rx mode  |          | 6              | 18      | mA   |
| Tx Characteristics                                       | Minimum  | Target setting | Maximum | Unit |
| Output Power   | 6.0      | 8.0            | 10.0    | dBm  |
| Spectrum Mask Margin                                     |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                          | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                       | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -45 dBr)                       | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-45 dBr)                             | 0        |                |         | dB   |
| Constellation Error (EVM)<br>(measured at enhanced mode) |          |                | -16     | dB   |
| Frequency Tolerance                                      | -20      |                | 20      | ppm  |
| Spurious Emissions                                       |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                             |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                             |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                          |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                          |          |                | -36     | dBm  |
| • 1000 - 12750 MHz (BW = 1 MHz)                          |          |                | -30     | dBm  |
| Rx Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER ≤ 10%)                          |          |                | -74     | dBm  |
| Maximum Input Level (PER < 10%)                          | -20      |                |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                   | 8        |                |         | dB   |

### 11.3.2 Low-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 9.5 dBm at module pad, MCS0 mode

**Table 25: Low-Rate Condition for IEEE 802.11n (HT20) - 2.4 GHz**

| Items   | Contents |         |         |      |
|---|----------|---------|---------|------|
|   | Minimum  | Typical | Maximum | Unit |
| <b>DC Characteristics</b>                                   |          |         |         |      |
| DC Current  |          |         |         |      |
| • Tx mode   |          | 80      | 110     | mA   |
| • Rx mode   |          | 6       | 18      | mA   |
| <b>Tx Characteristics</b>                                   |          |         |         |      |
| Output Power  |          |         |         |      |
|   | 7.5      | 9.5     | 11.5    | dBm  |
| Spectrum Mask Margin  |          |         |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                             | 0        |         |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                          | 0        |         |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -45 dBr)                          | 0        |         |         | dB   |
| • 30 MHz to 33 MHz (-45 dBr)                                | 0        |         |         | dB   |
| 4. Constellation Error (EVM)<br>(measured at enhanced mode) |          |         |         |      |
|   |          |         | -5      | dB   |
| Frequency Tolerance   |          |         |         |      |
|   | -20      |         | 20      | ppm  |
| Spurious Emissions  |          |         |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                                |          |         | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                                |          |         | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                              |          |         | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                             |          |         | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                              |          |         | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                              |          |         | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                              |          |         | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                              |          |         | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                             |          |         | -36     | dBm  |
| • 1000 - 12750 MHz (BW = 1 MHz)                             |          |         | -30     | dBm  |
| <b>Rx Characteristics</b>                                   |          |         |         |      |
| Minimum Input Level (PER ≤ 10%)                             |          |         |         |      |
|   |          |         | -82     | dBm  |
| Maximum Input Level (PER < 10%)                             |          |         |         |      |
|   | -20      |         |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                      |          |         |         |      |
|   | 16       |         |         | dB   |

## 11.4 DC/RF Characteristics for IEEE 802.11a - 5 GHz

**Table 26: Characteristics Values for IEEE 802.11a - 5 GHz**

| Items             | Contents   |
|-------------------|--|
| Specification     | IEEE 802.11a   |
| Mode              | OFDM   |
| Channel Frequency | 5180 to 5240 MHz, 5260 to 5320 MHz, 5500 to 5720 MHz, 5745 to 5825 MHz |
| Data Rate         | 6, 9, 12, 18, 24 Mbps  |

### 11.4.1 High-Rate Condition for IEEE 802.11a - 5 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 6.5 dBm at module pad, 24 Mbps mode

**Table 27: High-Rate Condition for IEEE 802.11a - 5 GHz**

| Items  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| DC Current   |          |                |         |      |
| • Tx mode  |          | 80             | 120     | mA   |
| • Rx mode  |          | 8              | 25      | mA   |
| Tx Characteristics                                       | Minimum  | Target setting | Maximum | Unit |
| Output Power   | 4.5      | 6.5            | 8.5     | dBm  |
| Spectrum Mask Margin                                     |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                          | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                       | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)                       | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)                             | 0        |                |         | dB   |
| Constellation Error (EVM)<br>(measured at enhanced mode) |          |                | -16     | dB   |
| Frequency Tolerance                                      | -20      |                | 20      | ppm  |
| Spurious Emissions                                       |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                             |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                             |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                          |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                          |          |                | -36     | dBm  |
| • 1000 - 5150 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5350 - 5470 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5725 - 26000 MHz (BW = 1 MHz)                          |          |                | -30     | dBm  |
| Rx Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER ≤ 10%)                          |          |                | -74     | dBm  |
| Maximum Input Level (PER < 10%)                          | -30      |                |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                   | 8        |                |         | dB   |

## 11.4.2 Low-Rate Condition for IEEE 802.11a - 5 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 8.0 dBm at module pad, 6 Mbps mode

**Table 28: Low-Rate Condition for IEEE 802.11a - 5 GHz**

| Items  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| DC Current   |          |                |         |      |
| • Tx mode  |          | 80             | 120     | mA   |
| • Rx mode  |          | 8              | 25      | mA   |
| Tx Characteristics                                       | Minimum  | Target setting | Maximum | Unit |
| Output Power   | 6.0      | 8.0            | 10.0    | dBm  |
| Spectrum Mask Margin                                     |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                          | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                       | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)                       | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)                             | 0        |                |         | dB   |
| Constellation Error (EVM)<br>(measured at enhanced mode) |          |                | -5      | dB   |
| Frequency Tolerance                                      | -20      |                | -20     | ppm  |
| Spurious Emissions                                       |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                             |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                             |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                          |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                          |          |                | -36     | dBm  |
| • 1000 - 5150 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5350 - 5470 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5725 - 26000 MHz (BW = 1 MHz)                          |          |                | -30     | dBm  |
| Rx Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER ≤ 10%)                          |          |                | -82     | dBm  |
| Maximum Input Level (PER < 10%)                          | -30      |                |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                   | 16       |                |         | dB   |

## 11.5 DC/RF Characteristics for IEEE 802.11n (HT20) - 5 GHz

**Table 29: Characteristics Values for IEEE 802.11n (HT20) - 5 GHz**

| Items             | Contents   |
|-------------------|--|
| Specification     | IEEE 802.11n   |
| Mode              | OFDM   |
| Channel Frequency | 5180 to 5240 MHz, 5260 to 5320 MHz, 5500 to 5720 MHz, 5745 to 5825 MHz |
| Data Rate         | MCS0-MCS3  |

### 11.5.1 High-Rate Condition for IEEE 802.11n (HT20) - 5 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 6.5 dBm at module pad, MCS3 mode

**Table 30: High-Rate Condition for IEEE 802.11n (HT20) - 5 GHz**

| Items  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| DC Current   |          |                |         |      |
| • Tx mode  |          | 80             | 120     | mA   |
| • Rx mode  |          | 8              | 25      | mA   |
| Tx Characteristics                                       | Minimum  | Target setting | Maximum | Unit |
| Output Power   | 4.5      | 6.5            | 8.5     | dBm  |
| Spectrum Mask Margin                                     |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                          | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                       | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)                       | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)                             | 0        |                |         | dB   |
| Constellation Error (EVM)<br>(measured at enhanced mode) |          |                | -16     | dB   |
| Frequency Tolerance                                      | -20      |                | 20      | ppm  |
| Spurious Emissions                                       |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                             |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                             |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                          |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                          |          |                | -36     | dBm  |
| • 1000 - 5150 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5350 - 5470 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5725 - 26000 MHz (BW = 1 MHz)                          |          |                | -30     | dBm  |
| Rx Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER ≤ 10%)                          |          |                | -74     | dBm  |
| Maximum Input Level (PER < 10%)                          | -30      |                |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                   | 8        |                |         | dB   |

## 11.5.2 Low-Rate Condition for IEEE 802.11n (HT20) - 5 GHz

**Conditions:** 25 °C, VBAT = 3.3V, VIO = 1.8V, Output power setting = 8.0 dBm at module pad, MCS0 mode


**Table 31: Low-Rate Condition for IEEE 802.11n (HT20) - 5 GHz**

| Items  | Contents |                |         |      |
|--|----------|----------------|---------|------|
| DC Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| DC Current   |          |                |         |      |
| • Tx mode  |          | 80             | 120     | mA   |
| • Rx mode  |          | 8              | 25      | mA   |
| Tx Characteristics                                       | Minimum  | Target setting | Maximum | Unit |
| Output Power   | 6.0      | 8.0            | 10.0    | dBm  |
| Spectrum Mask Margin                                     |          |                |         |      |
| • 9 MHz to 11 MHz (0 ~ -20 dBr)                          | 0        |                |         | dB   |
| • 11 MHz to 20 MHz (-20 ~ -28 dBr)                       | 0        |                |         | dB   |
| • 20 MHz to 30 MHz (-28 ~ -40 dBr)                       | 0        |                |         | dB   |
| • 30 MHz to 33 MHz (-40 dBr)                             | 0        |                |         | dB   |
| Constellation Error (EVM)<br>(measured at enhanced mode) |          |                | -5      | dB   |
| Frequency Tolerance                                      | -20      |                | 20      | ppm  |
| Spurious Emissions                                       |          |                |         |      |
| • 30 - 47 MHz (BW = 100 kHz)                             |          |                | -36     | dBm  |
| • 47 - 74 MHz (BW = 100 kHz)                             |          |                | -54     | dBm  |
| • 74 - 87.5 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 87.5 - 118 MHz (BW = 100 kHz)                          |          |                | -54     | dBm  |
| • 118 - 174 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 174 - 230 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 230 - 470 MHz (BW = 100 kHz)                           |          |                | -36     | dBm  |
| • 470 - 862 MHz (BW = 100 kHz)                           |          |                | -54     | dBm  |
| • 862 - 1000 MHz (BW = 100 kHz)                          |          |                | -36     | dBm  |
| • 1000 - 5150 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5350 - 5470 MHz (BW = 1 MHz)                           |          |                | -30     | dBm  |
| • 5725 - 26000 MHz (BW = 1 MHz)                          |          |                | -30     | dBm  |
| Rx Characteristics                                       | Minimum  | Typical        | Maximum | Unit |
| Minimum Input Level (PER ≤ 10%)                          |          |                | -82     | dBm  |
| Maximum Input Level (PER < 10%)                          | -30      |                |         | dBm  |
| Adjacent Channel Rejection (PER ≤ 10%)                   | 16       |                |         | dB   |

## 12 Land Pattern

The land pattern is shown in **Figure 8**.

**Figure 8: Land Pattern (TOP VIEW)**



## 13 Tape and Reel Packing


This section contains the following topics:

- Dimensions of Tape (Plastic tape)
- Dimensions of Reel
- Taping Diagrams
- Leader and tail tape
- Packaging

### 13.1 Dimensions of Tape (Plastic Tape)

Figure 9 is a graphical representation of the tape dimension (plastic tape)<sup>1</sup>.

Figure 9: Dimensions of Tape (Unit: mm)




<sup>1</sup> Cumulative tolerance of max 40 +/-0.15 mm for every 10 pitches.

## 13.2 Dimension of Reel

Figure 10 shows the reel dimensions.

Figure 10: Dimensions of Reel (Unit: mm)



### 13.3 Taping Diagrams

Figure 11 and Figure 12 shows the tapings diagrams.

Figure 11: Taping Diagrams





Table 32: Taping Specifications

| Mark | Description   |
|------|---|
| 1    | Feeding Hole. As specified in <a href="#">Dimensions of Tape (Plastic tape)</a> ☐.  |
| 2    | Hole for chip. As specified in <a href="#">Dimensions of Tape (Plastic tape)</a> ☐. |
| 3    | Cover tape. 62 μm in thickness.   |
| 4    | Base tape. As specified in <a href="#">Dimensions of Tape (Plastic tape)</a> ☐.     |


Figure 12: Taping Diagrams (Close Up)



## 13.4 Leader and Tail Tape


The leader and tail tape are shown in **Figure 13**.

**Figure 13: Leader and Tail Tape**



- The tape for chips is wound clockwise, the feeding holes to the right side as the tape is pulled toward the user.
- The cover tape and base tape are not adhered at no components area for 250 mm minimum.
- Tear off strength against pulling of cover tape: 5 N minimum.
- Packaging unit: 1000 pcs. / Reel
- Tape material:
  - Base tape: Plastic
  - Reel: Plastic
  - Cover tape, cavity tape and reel are made the anti-static processing.
- Peeling off force: 1.1 N maximum in the direction of peeling as shown in **Figure 14**.


**Figure 14: Peeling Force**



## 13.5 Packaging (Humidity Proof Packing)

Figure 15 shows the humidity proof Packaging.

Figure 15: Humidity Proof Packaging



Tape and reel must be sealed with the anti-humidity plastic bag. The bag contains the desiccant and the humidity indicator.

## 14 Notice

### 14.1 Storage Conditions

- Please use this product within 6 months after receipt.
- The product shall be stored without opening the packing under the ambient temperature from 5 to 35 °C and humidity from 20 ~ 70 %RH (Packing materials may be deformed at the temperature over 40 °C).
- The product left more than 6 months after reception; the solderability needs to be confirmed before it is used.
- The product shall be stored in non-corrosive gas (Cl<sub>2</sub>, NH<sub>3</sub>, SO<sub>2</sub>, NO<sub>x</sub>, etc.).
- Any excess mechanical shock including, but not limited to, sticking the packing materials by sharp object, and dropping the product, shall not be applied in order not to damage the packing materials.
- This product is applicable to MSL3 (Based on IPC/JEDEC J-STD-020)
  - After the packing opened, the product shall be stored at <30 °C / <60 %RH and the product shall be used within 168 hours.
  - When the color of the indicator in the packing changed, the product shall be baked before soldering.
- Baking condition: 125 +5/-0 °C, 24 hours, 1 time
- The products shall be baked on the heat-resistant tray because the material (Base Tape, Reel Tape and Cover Tape) is not heat-resistant.

### 14.2 Handling Conditions

- Be careful in handling or transporting products because excessive stress or mechanical shock may break products.
- Handle with care if products may have cracks or damages on their terminals, the characteristics of products may change. Do not touch products with bare hands that may result in poor solder ability and destroy by static electrical charge.

### 14.3 Standard PCB Design (Land Pattern and Dimensions)

- All the ground terminals should be connected to the ground patterns. Furthermore, the ground pattern should be provided between IN and OUT terminals. Please refer to the specifications for the standard land dimensions.
- The recommended land pattern and dimensions is as Murata's standard. The characteristics of products may vary depending on the pattern drawing method, grounding method, land dimensions, land forming method of the NC terminals and the PCB material and thickness. Therefore, be sure to verify the characteristics in the actual set. When using non-standard lands, contact Murata beforehand.

## 14.4 Notice for Chip Placer


When placing products on the PCB, products may be stressed and broken by uneven forces from a worn-out chucking locating claw or a suction nozzle. To prevent products from damages, be sure to follow the specifications for the maintenance of the chip placer being used. For the positioning of products on the PCB, be aware that mechanical chucking may damage products.

## 14.5 Soldering Conditions

The recommendation conditions of soldering are shown in **Figure 16**.

Soldering must be carried out by the above-mentioned conditions to prevent products from damage. Set up the highest temperature of reflow within 260 °C. Contact Murata before use if concerning other soldering conditions.

**Figure 16: Reflow Soldering Standard Conditions (Example)**



Please use the reflow within 2 times.  
Use rosin type flux or weakly active flux with a chlorine content of 0.2 wt. % or less.

## 14.6 Cleaning

This product is moisture sensitive; therefore, any cleaning is not recommended. If any cleaning process is done the customer is responsible for any issues or failures caused by the cleaning process.

## 14.7 Operational Environment Conditions

Products are designed to work for electronic products under normal environmental conditions (ambient temperature, humidity, and pressure). Therefore, products have no problems to be used under the similar conditions to the above-mentioned. However, if products are used under the following circumstances, it may damage products and leakage of electricity and abnormal temperature may occur.

- In an atmosphere containing corrosive gas (Cl<sub>2</sub>, NH<sub>3</sub>, SO<sub>x</sub>, NO<sub>x</sub> etc.).
- In an atmosphere containing combustible and volatile gases.
- Dusty place.
- Direct sunlight place.
- Water splashing place.
- Humid place where water condenses.
- Freezing place.



If there are possibilities for products to be used under the preceding clause, consult with Murata before actual use.



Do not apply static electricity or excessive voltage while assembling and measuring, as it might be a cause of degradation or destruction to apply static electricity to products.

## 15 Preconditions to Use Our Products



PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product when our product is mounted to your product.

All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the products is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIM ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

You agree that you will use any and all software or program code (including but not limited to firmware, and radio configuration files) we may provide or to be embedded into our product ("Software") provided that you use the Software bundled with our product. YOU AGREE THAT THE SOFTWARE SHALL BE PROVIDED TO YOU "AS IS" BASIS, MURATA MAKES NO REPRESENTATIONS OR WARRANTIES THAT THE SOFTWARE IS ERROR-FREE OR WILL OPERATE WITHOUT INTERRUPTION. AND MORE, MURATA MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED WITH RESPECT TO THE SOFTWARE. MURATA EXPRESSLY DISCLAIM ANY AND ALL WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE NOR THE WARRANTY OF TITLE OR NON-INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

You shall indemnify and hold harmless us, our affiliates, and our licensor from and against any and all claims, costs, expenses and liabilities (including attorney's fees), which arise in connection with the using the Software.

The product shall not be used in any application listed below which requires especially high reliability for the prevention of such defect as may directly cause damage to the third party's life, body or property. You acknowledge and agree that, if you use our products in such applications, we will not be responsible for any failure to meet such requirements. Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS AND THE SOFTWARE IN SUCH APPLICATIONS.

- Aircraft equipment.
- Aerospace equipment.
- Undersea equipment.
- Power plant control equipment.
- Medical equipment.
- Traffic signal equipment.

- Burning / explosion control equipment.
- Disaster prevention / crime prevention equipment.
- Transportation equipment (vehicles, trains, ships, elevator, etc.).
- Application of similar complexity and/ or reliability requirements to the applications listed in the above.
- We expressly prohibit you from analyzing, breaking, reverse-engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

Even in the unlikely event that an abnormality or malfunction occurs in this product under operating conditions that conform to the specifications, be sure to add an appropriate fail-safe function to the system to prevent secondary accidents.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use.

Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

By signing on specification sheet or approval sheet, you acknowledge that you are the legal representative for your company and that you understand and accept the validity of the contents herein. When you are not able to return the signed version of specification sheet or approval sheet within 30 days from receiving date of specification sheet or approval sheet, it shall be deemed to be your consent on the content of specification sheet or approval sheet. Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status. We reject any liability or product warranty for engineering samples. In particular we disclaim liability for damages caused by

- The use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the product to be sold by you,
- Deviation or lapse in function of engineering sample,
- Improper use of engineering samples.
- We disclaim any liability for consequential and incidental damages.

This Precondition to Use Our Products stipulated in this datasheet can only be modified, amended or altered by documents that explicitly reflect the mutual consent of both parties (including instances where one party explicitly indicates its acceptance of terms provided by the other party through click-through agreements).

If you can't agree with the above contents, please contact sales.

## Revision History

| Revision Code | Date       | Changed Item  | Comment   |
|---------------|------------|---|---|
| 1             | 2025.08.25 |   | Initial release.<br>Base IC datasheet revision: AF  |
| 2             | 2025.12.18 | 2 Key Features<br>4 Block Diagram<br>6 Dimensions, Marking and Terminal ...<br>5.1 Certification Information<br>5.2 5.2 Radio Regulatory Certification by Country<br>11 DC / RF Characteristics<br><br>8 Absolute Maximum Rating<br>9.1 Operating Conditions<br>9.4 Power modes<br>9.5 Package Thermal Condition<br>11.1 DC/RF Characteristics for IEEE 802.11b<br>12 Land Pattern<br>13.1 Dimensions of Tape (Plastic Tape)<br>13.2 Dimension of Reel<br>13.4 Leader and Tail Tape | <ul style="list-style-type: none"> <li>• Added Dimension and FIT.</li> <li>• Changed VCC to 1V8</li> <li>• Added side view</li> <li>• Added TBD</li> <li>• Added this section.</li> <li>• Updated Tx power and Current consumption</li> <li>• Added VIO max</li> <li>• Updated VIO max</li> <li>• Corrected typo</li> <li>• Defined RΨjt</li> <li>• Added information about short preamble.</li> <li>• Added land pattern</li> <li>• Added Figure 11</li> <li>• Added Figure 12</li> <li>• Added quantity of a reel</li> </ul> Base IC datasheet revision: AF |
| 3             | 2026.02.17 | 5.1 Radio Certification<br>7.2 Pin Descriptions<br><br>7.5 I/O Mux Table  | <ul style="list-style-type: none"> <li>• Updated US/CA/TW/ANZ</li> <li>• Pin 43 GPIO_8 : Added comments</li> <li>• Pin 1,2,3,4,44,45 Added comments</li> <li>• Added SPI_INT</li> </ul>   |



Copyright © Murata Manufacturing Co., Ltd. All rights reserved. The information and content in this document are provided “as-is” with no warranties of any kind and are for informational purpose only. Data and information have been carefully checked and are believed to be accurate; however, no liability or responsibility for any errors, omissions, or inaccuracies is assumed.

Wi-Fi® is a registered trademark of Wi-Fi Alliance. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. Other brand and product names are trademarks or registered trademarks of their respective owners.

Specifications are subject to change without notice.