


Typical unit

FEATURES

- DC-DC converter with supporting IEEE 802.3af class0 (MYBSP00502ABFS, MYBSP01201ABFS), IEEE 802.3af class1 (MYBSP00502ABFT, MYBSP01201ABFT) and IEEE 802.3af class2 (MYBSP00502ABFU, MYBSP01201ABFU)
- 37-57V Input Voltage range
- 14.8 x 26 x 6 mm Size
- 83.4% typical efficiency for MYBSP00502ABFS, 86.0% typical efficiency for MYBSP01201ABFS
- PWM Control (Fixed Frequency)
- Surface mount module
- 2250V Input-Output Isolation
- Operating Temperature range -40 to 85 degC

PRODUCT OVERVIEW

MYBSP00502ABFS / MYBSP00502ABFT / MYBSP00502ABU / MYBSP01201ABFS / MYBSP01201ABFT / MYBSP01201ABU are an isolated, regulated, DC-DC converter for PoE PD that has an input range of 37-57V with a typical efficiency of 83.4%(MYBSP00502ABFS), 86.0%(MYBSP01201ABFS) and full 2250 Volt DC isolation. The products are ideal for IEEE 802.3af Compliant Devices. The modules have self-protection features. These include input undervoltage lockout and output current limit. And the modules have detection and classification for compliant IEEE 802.3af.



Note: There are two types of power supply method: Alternative A and Alternative B.
Alternative A: A method that uses the data and power supply lines of 10BASE-T/100BASE-TX in common. It uses pins 1, 2, 3 and 6 of the RJ45 connector.
Alternative B: Pins 1, 2, 3 and 6 of the RJ45 connector are used for the 10BASE-T/100BASE-TX data lines. On the other hand, pins 4, 5, 7 and 8 of the RJ45 connector, which are not used for the 10BASE-T/100BASE-TX data lines, are used for the power supply lines.


Figure 1. Simplified Block Diagram
Typical topology is shown.

PERFORMANCE SPECIFICATIONS SUMMARY AND ORDERING GUIDE


Model Number	Output						Input			Efficiency [%]		Package [mm]
	V _{OUT} [V]	I _{OUT} (Max.) [A]	Power [W]	R/N Typ. [mVp-p]	Regulation Typ.		V _{IN} Nom. [V]	Range [V]	I _{IN} full load (Typ.) [A]	Min.	Typ.	
					Line [%]	Load [%]						
MYBSP00502ABFS	5	2	10	100	±0.6	±0.5	48	37-57	0.25	79.4	83.4	14.8 x 26 x 6
MYBSP00502ABFT	5	0.8	3.84	100	±0.6	±0.5	48	37-57	0.10	77.0	81.0	14.8 x 26 x 6
MYBSP00502ABFU	5	1.3	6.49	100	±0.6	±0.5	48	37-57	0.16	78.5	82.5	14.8 x 26 x 6
MYBSP01201ABFS	12	1	10	50	±0.6	±0.5	48	37-57	0.29	82.0	86.0	14.8 x 26 x 6
MYBSP01201ABFT	12	0.35	3.84	50	±0.6	±0.5	48	37-57	0.11	78.0	82.0	14.8 x 26 x 6
MYBSP01201ABFU	12	0.55	6.49	50	±0.6	±0.5	48	37-57	0.16	80.0	84.0	14.8 x 26 x 6

1. Please refer to the Part Number Structure for additional ordering information and options.
2. All specifications are at nominal line voltage, full load, 25degC unless otherwise stated.

PART NUMBER STRUCTURE



Product Marking



Codes

Murata Manufacturing ID

Product Code

Part Number	Product Code
MYBSP00502ABFS	EP
MYBSP00502ABFT	
MYBSP00502ABFU	

Part Number	Product Code
MYBSP01201ABFS	EQ
MYBSP01201ABFT	
MYBSP01201ABFU	

Internal Manufacturing ID

Internal Code

Part Number	Internal Code
MYBSP00502ABFS	(Blank)
MYBSP00502ABFT	1
MYBSP00502ABFU	2

Part Number	Internal Code
MYBSP01201ABFS	(Blank)
MYBSP01201ABFT	1
MYBSP01201ABFU	2

FUNCTIONAL SPECIFICATIONS, MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU

ABSOLUTE MAXIMUM RATINGS	Conditions	Minimum	Typical / Nominal	Maximum	Units	
Input Voltage, Continuous		0	-	57	V	
Input Voltage, Transient	100ms max. duration	-	-	60	V	
Isolation Voltage	Input to output, Leak current 1mA max for 1minute at 25degC/60%RH.	-	-	2250	V	
Output Power		0	-	10	W	
Output Current	Current-limited, no damage, short-circuit protected	0	-	2	A	
Storage Temperature Range	$V_{IN} = \text{Zero (no power)}$	-40	-	90	degC	
Absolute maximums are stress ratings. Exposure of devices to greater than any of these conditions may adversely affect long-term reliability. Proper operation under conditions other than those listed in the Performance/Functional Specifications Table is not implied or recommended.						
INPUT						
Operating Voltage Range	Slew rate less than 30V/us	37	48	57	V	
Start-up threshold	Rising input voltage	35.5	37.5	40.5	V	
Undervoltage shutdown	Falling input voltage	29.5	32	33.5	V	
Internal Filter Type		-	Pi	-		
Input current						
Full Load Conditions	$V_{IN} = \text{nom.}, I_{OUT} = \text{max}$	-	0.25	-	A	
Low Line Input current	$V_{IN} = \text{min.}, I_{OUT} = \text{max.}$	-	0.33	-	A	
On Resistance of Internal Hotswap		-	0.5	-	Ω	
Resistance for detection	$V_{IN} = 2.7$ to 10.1V	-	25	-	k Ω	
Classification current	$V_{IN} = 14.5$ to 20.5V	MYBSP00502ABFS	-	2	-	mA
		MYBSP00502ABFT	-	10.5	-	mA
		MYBSP00502ABFU	-	18.5	-	mA
GENERAL and SAFETY						
Efficiency	$V_{IN} = 48V, I_{OUT} = 2A$	79.4	83.4	-	%	
	$V_{IN} = 48V, I_{OUT} = 0.8A$	77.0	81.0	-	%	
	$V_{IN} = 48V, I_{OUT} = 1.3A$	78.5	82.5	-	%	
Isolation						
Isolation Voltage	Input to output, Leak current 1mA max for 1minute at 25degC/60%RH.	2250	-	-	V	
Insulation Safety Rating		-	Functional	-		
Isolation Capacitance		-	1500	-	pF	
Calculated MTBF	Telcordia SR-332, issue 1, class 3, ground fixed, $T_a = 25\text{degC}$	-	5984	-	Hours x 10 ³	
DYNAMIC CHARACTERISTIC						
Fixed Switching Frequency	$V_{IN} = 48V, I_{OUT} = \text{max}$	-	450	-	kHz	
V_{OUT} Rise Time	From 10-90% of V_{OUT}	-	6	-	ms	
Dynamic Load Peak Deviation	50-100-50% load step, SR = 0.66A/usec	-	350	-	mV	

FUNCTIONAL SPECIFICATIONS, MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU

OUTPUT	Conditions	Minimum	Typical / Nominal	Maximum	Units
Total Output Power		0	-	10	W
Voltage					
Nominal Output Voltage	$I_{OUT} = 0.2A$ to max *1	4.7	5	5.3	V
Overvoltage Protection		-	None	-	V
Current					
Output Current Range *2		0	-	2	A
Current Limit Inception		2.1	-	-	A
Short circuit protection method		-	Hiccup	-	
Regulation					
Line Regulation	$V_{IN} = \text{min. to max.}, V_{OUT} = \text{nom.}, \text{full load}$	-	0.6	-	% of V_{OUT}
Load Regulation	$I_{OUT} = 0.2A$ to max.	-	0.5	-	% of V_{OUT}
Ripple and Noise	150 MHz BW, $C_{OUT} = 0.1\mu F$ MLCC paralleled with 10 μF and 47 $\mu F \times 2$	-	100	300	mV pk-pk
Maximum Capacitive Loading	Low ESR	100	-	600	μF
MECHANICAL					
Outline Dimensions	L x W x H	-	14.8 x 26 x 6	-	mm
Weight		-	4.7	-	Grams
Pin Diameter		-	1.6	-	mm
Pin Material		-	Copper alloy	-	
ENVIRONMENTAL					
Operating Ambient Temperature Range		-40	-	85	degC
Storage Temperature	$V_{IN} = \text{Zero (no power)}$	-40	-	90	degC
Electromagnetic Interference Conducted, EN55022/CISPR22	External filter is required	-	A	-	Class
Moisture Sensitivity Level			1 Equivalent		

Specification Notes


Unless otherwise noted, all specifications are typical at nominal input voltage, nominal output voltage and full load. General conditions are 25degC ambient temperature, near sea level altitude, natural convection airflow. All models are tested and specified with external parallel 0.1 μF and 10 μF and 100 μF output capacitors (See Technical Notes).

- *1 Maximum output voltage is 6V if I_{OUT} is less than 0.2A.
- *2 Input current must be greater than or equal to 10mA if your application applies Maintain Power Signature(MPS) by IEEE802.3af. Please check with your application.


In this document, all characteristics are measured with the test board. The schematic and part list of the board are shown in the test circuit on 14 pages. The board is under $T_a = 25\text{degC}$ with no airflow unless otherwise noted.

PERFORMANCE DATA, MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU


Efficiency vs. Line Voltage and Load Current




Load Regulation




V_{OUT} Start-up
($V_{IN} = 48V, I_{OUT} = 2A$)



Output Ripple and Noise
($V_{IN} = 48V, I_{OUT} = 2A$)




Transient Response
($V_{IN} = 48V, C_{OUT} = 47\mu F \times 2\text{pcs}, I_{OUT} = 1 \text{ to } 2A$)




Thermal Derating

Unit under test (UUT) is covered by acrylic box to avoid airflow.
($V_{IN} = 48V$, See Technical Notes)




PERFORMANCE DATA, MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU (CONT.)


Conduction Noise ($V_{IN} = 48V, I_{OUT} = 2A, T_a = 25degC$)
with External Filter




Conduction Noise ($V_{IN} = 48V, I_{OUT} = 2A, T_a = 25degC$)
with External Filter



Radiation Noise ($V_{IN} = 48V, I_{OUT} = 2A, T_a = 25degC$)
without External Filter



Radiation Noise ($V_{IN} = 48V, I_{OUT} = 2A, T_a = 25degC$)
without External Filter



FUNCTIONAL SPECIFICATIONS, MYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU

ABSOLUTE MAXIMUM RATINGS	Conditions	Minimum	Typical / Nominal	Maximum	Units	
Input Voltage, Continuous		0	-	57	V	
Input Voltage, Transient	100ms max. duration	-	-	60	V	
Isolation Voltage	Input to output, Leak current 1mA max for 1minute at 25degC/60%RH.	-	-	2250	V	
Output Power		0	-	12	W	
Output Current	Current-limited, no damage, short-circuit protected	0	-	1	A	
Storage Temperature Range	$V_{IN} = \text{Zero}$ (no power)	-40	-	90	degC	
Absolute maximums are stress ratings. Exposure of devices to greater than any of these conditions may adversely affect long-term reliability. Proper operation under conditions other than those listed in the Performance/Functional Specifications Table is not implied or recommended.						
INPUT						
Operating Voltage Range	Slew rate less than 30V/us	37	48	57	V	
Start-up threshold	Rising input voltage	35.5	37.5	40.5	V	
Undervoltage shutdown	Falling input voltage	29.5	32	33.5	V	
Internal Filter Type		-	Pi	-		
Input current						
Full Load Conditions	$V_{IN} = \text{nom.}, I_{OUT} = \text{max}$	-	0.29	-	A	
Low Line Input current	$V_{IN} = \text{min.}, I_{OUT} = 0.9A *3$	-	0.34	-	A	
On Resistance of Internal Hotswap		-	0.5	-	Ω	
Resistance for detection	$V_{IN} = 2.7$ to 10.1V	-	25	-	k Ω	
Classification current	$V_{IN} = 14.5$ to 20.5V	MYBSP01201ABFS	-	2	-	mA
		MYBSP01201ABFT	-	10.5	-	mA
		MYBSP01201ABFU	-	18.5	-	mA
GENERAL and SAFETY						
Efficiency	$V_{IN} = 48V, I_{OUT} = 1A$	82.0	86.0	-	%	
	$V_{IN} = 48V, I_{OUT} = 0.35A$	78.0	82.0	-	%	
	$V_{IN} = 48V, I_{OUT} = 0.55A$	80.0	84.0	-	%	
Isolation						
Isolation Voltage	Input to output, Leak current 1mA max for 1minute at 25degC/60%RH.	2250	-	-	V	
Insulation Safety Rating		-	Functional	-		
Isolation Capacitance		-	1500	-	pF	
Calculated MTBF	Telcordia SR-332, issue 1, class 3, ground fixed, $T_a = 25\text{degC}$	-	5741	-	Hours x 10 ³	
DYNAMIC CHARACTERISTIC						
Fixed Switching Frequency	$V_{IN} = 48V, I_{OUT} = \text{max}$	-	420	-	kHz	
V_{OUT} Rise Time	From 10-90% of V_{OUT}	-	27.5	-	ms	
Dynamic Load Peak Deviation	50-100-50% load step, SR = 0.9A/usec	-	600	-	mV	


FUNCTIONAL SPECIFICATIONS, MYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU

OUTPUT	Conditions	Minimum	Typical / Nominal	Maximum	Units
Total Output Power		0	-	12	W
Voltage					
Nominal Output Voltage	$I_{OUT} = 0.1A$ to max *1	11.4	12	12.6	V
Overvoltage Protection		-	None	-	V
Current					
Output Current Range *2		0	-	1	A
Current Limit Inception *3		1.05	-	-	A
Short circuit protection method		-	Hiccup	-	
Regulation					
Line Regulation	$V_{IN} = \text{min. to max.}, V_{OUT} = \text{nom.}, \text{full load}$	-	0.6	-	% of V_{OUT}
Load Regulation	$I_{OUT} = 0.3A$ to max.	-	0.5	-	% of V_{OUT}
	$I_{OUT} = 0.1A$ to max.	-	1.0	-	% of V_{OUT}
Ripple and Noise	150 MHz BW, $C_{OUT} = 0.1\mu F$ MLCC paralleled with 10 μF	-	50	100	mV pk-pk
Maximum Capacitive Loading	Low ESR	88	-	400	μF
MECHANICAL					
Outline Dimensions	L x W x H	-	14.8 x 26 x 6	-	mm
Weight		-	4.7	-	Grams
Pin Diameter		-	1.6	-	mm
Pin Material		-	Copper alloy	-	
ENVIRONMENTAL					
Operating Ambient Temperature Range		-40	-	85	degC
Storage Temperature	$V_{IN} = \text{Zero (no power)}$	-40	-	90	degC
Electromagnetic Interference Conducted, EN55022/CISPR22	External filter is required	-	A	-	Class
Moisture Sensitivity Level			1 Equivalent		

Specification Notes

Unless otherwise noted, all specifications are typical at nominal input voltage, nominal output voltage and full load. General conditions are 25degC ambient temperature, near sea level altitude, natural convection airflow. All models are tested and specified with external parallel 0.1 μF and 10 μF and 100 μF output capacitors (See Technical Notes).


- *1 Maximum output voltage is 14.4V if I_{OUT} is less than 0.1A.
- *2 Input current must be greater than or equal to 10mA if your application applies Maintain Power Signature(MPS) by IEEE 802.3af. Please check with your application.
- *3 Input current overcurrent protection limits output power at low input voltage. Refer to the following graph for input voltage vs. output power. Therefore, output power must be lowered less than power shown the graph.




In this document, all characteristics are measured with the test board. The schematic and part list of the board are shown in the test circuit on 14 pages. The board is under $T_a = 25\text{degC}$ with no airflow unless otherwise noted.

PERFORMANCE DATA, MYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU

Efficiency vs. Line Voltage and Load Current




Load Regulation



V_{OUT} Start-up
($V_{IN} = 48V, I_{OUT} = 1A$)



Output Ripple and Noise
($V_{IN} = 48V, I_{OUT} = 1A$)



Transient Response
($V_{IN} = 48V, C_{OUT} = 22\mu F \times 4\text{pcs}, I_{OUT} = 0.5 \text{ to } 1A, 0.9A/\mu s$)




Transient Response
($V_{IN} = 48V, C_{OUT} = 22\mu F \times 4\text{pcs}, I_{OUT} = 1 \text{ to } 0.5, 0.9A/\mu s$)




PERFORMANCE DATA, MYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU (CONT.)


Thermal Derating
Unit under test (UUT) is covered by acrylic box to avoid airflow.
(VIN = 48V, See Technical Notes)




Conduction Noise (VIN = 48V, IOUT = 1A, Ta = 25degC) with External Filter




Conduction Noise (VIN = 48V, IOUT = 1A, Ta = 25degC) with External Filter




Radiation Noise (VIN = 48V, IOUT = 1A, Ta = 25degC) with External Filter



Radiation Noise (VIN = 48V, IOUT = 1A, Ta = 25degC) with External Filter




MECHANICAL SPECIFICATIONS




[Unit : mm]

INPUT / OUTPUT CONNECTIONS			
Pin	Designation	Function	Pin size
1	+V _{IN}	Positive Input Voltage	$\phi 1.6$
2	-V _{IN}	Negative Input Voltage	$\phi 1.6$
3	-V _{OUT}	Negative Output Voltage	$\phi 1.6$
4	+V _{OUT}	Positive Output Voltage	$\phi 1.6$

RECOMMENDED FOOTPRINT (Top View) & RECOMMENDED METAL MASK DESIGN




*Avoid placing pattern layout in hatched area to insulate between pattern and DC-DC converter.



[Unit : mm]

PACKAGING INFORMATION (SURFACE MOUNT, MSL Rating 1 Equivalent)

Packaging form
Tray Specification






Pieces of contained products per corrugated box.
Maximum contained products pieces 200 pcs/corrugated box.

Further plural sheets of corrugated cardboard are placed on the top of the tray cover according to number of contained trays in order to fill up the space in a corrugated box.

PACKAGING INFORMATION (SURFACE MOUNT, MSL Rating 1 Equivalent)

Packaging form
Tray Specification



TECHNICAL NOTES

Over Current Protection


Over Current Protection operates with a controller circuit failure or over-load condition. After rejected the abnormal mode, DC-DC converter will automatically restart. However, output short voltage affect long-term reliability.

External Input Capacitor

Do not connect any capacitor between positive input and negative input to avoid large inrush current. It is one of the requirements of IEEE802.3af standard.

Test Circuit

The initial values in Functional Specification are measured in the following test circuit.



C1 : Ceramic Capacitor: 47uFx2pcs (MYBSP00502ABFx)
22uFx4pcs (MYBSP01201ABFx)

RL : Electronic Load Device: LN-1000A-G7 KEISOKU GIKEN equivalent


V_{IN} : DC Power Supply: Model HP6675A KEYSIGHT equivalent

V : Digital Multimeter: Model HP34401A KEYSIGHT equivalent

When deviating from the above, DC-DC converter may operate abnormally. It should be fully confirmed on your board before use.

Ripple Noise Test

Output ripple noise is measured using designated external output components, circuits and layout as shown below.




C1 : Ceramic Capacitor: 47uFx2pcs (MYBSP00502ABFx)
22uFx4pcs (MYBSP01201ABFx)

C2 : Ceramic Capacitor 0.1uF


C3 : Ceramic Capacitor 10uF

Conduction Noise

The external input filter is installed and the circuit diagram is shown below.




(a) MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU




(b) MYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU

Radiation Noise



(a) MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU



(b) MYMYBSP01201ABFS, MYBSP01201ABFT, MYBSP01201ABFU

Thermal Derating Condition



The output current is limited by the derating curve. The derating curve in this datasheet illustrate typical operation under a variety of conditions.

DC-DC Converter is tested on a 101.6x188mm, 2 layers Copper evaluation board at $V_{IN} = 48V$.

The Unit Under Test (UUT) is set up as shown below. UUT is covered by acrylic box to avoid airflow.

The temperature measurement points are shown below table. The temperature of measurement points should not exceed the maximum temperatures in the below table.

Position	Description	Max temperature
P1	IC	$T_{P1MAX} = 110degC$
P2	Diode	$T_{P2MAX} = 124degC$
P3	Transformer pattern	$T_{P3MAX} = 125degC$



Detection and Hardware Classification

DC-DC converter implements IEEE 802.3af compliant detection and hardware classification.


When DC-DC converter(PD) is connected to PSE, the PSE applies two voltages in the range of 2.8 to 10 V and measures the corresponding current. Connection to PD is detected by measured current.(Detection)

After Detection, the PSE applies voltage in the range of 15.5 to 20.5 V and measures the corresponding current. PD is classified by measured current.(Hardware Classification)

Please check with your application.

Power Demotion

Power Demotion allows the PSE to supply power to a PD even if the PSE does not have all of the PD's requested power available. Also it allows higher power PDs to operate in a reduced mode when connected to lower power PSEs.




Power Demotion				
Type Power	PSE Power Available	PD(12.9W) Class 0 Requested	PD(3.84W) Class 1 Requested	PD(6.49W) Class 2 Requested
Type 1	15.4W	12.9W	3.84W	6.49W
	4W	3.84W	3.84W	3.84W
	7W	6.49W	3.84W	6.49W
Type 2	15.4W	12.9W	3.84W	6.49W
Type 3	30W	12.9W	3.84W	6.49W
	45W	12.9W	3.84W	6.49W
Type 4	60W	12.9W	3.84W	6.49W
	75W	12.9W	3.84W	6.49W
	90W	12.9W	3.84W	6.49W

SMT Reflow Soldering Guidelines

The surface-mount reflow solder profile is shown below.
This graph should be used only as a guideline.

Reflow Soldering Profiles : JEDEC IPC/JEDEC J-STD-020D

Soldering temperature	245degC +/-5degC
Soldering time	30 seconds, 240-245degC
Heating time	60~150 seconds, 217degC min.
Preheat time	60~120 seconds, 150-200degC
Programming rate	3degC /sec.max., 217-245degC
Descending rate	6degC /sec.max.
Total soldering time	8 minutes max., 25-245degC
Time	1time



Do not vibrate for the products on reflow. Please need to take care temperature control because mounted parts may come off if the product is left under the high temperature. Do not mount on backside of the board.

Many other factors influence the success of SMT reflow soldering. Since your production environment may differ, please thoroughly review these guidelines with your process engineers.

Storage

Please store the products in room where direct sunlight cannot come in and use the products within 6 months after delivery and maintain an appropriate storage condition using the following conditions.

- A temperature is +5 degC to +40 degC and a relative humidity is 20% to 70% as a standard condition. The temperature recommendation is less than 30 degC.
- If the storage period exceeds six months, check packaging, mounting, etc. before use.
- In addition, this may cause oxidation of the electrodes. If more than one year has elapsed since delivery, also check the solderability before use.
- Please do not store the products in the places such as: in a dusty place, in a place exposed directly to sea breeze, in an atmosphere containing corrosive gas (Cl₂, NH₃, SO₂, NO_x and so on).

This product is MSL1.

After opening bags, please store the products under maximum condition of 30degC, 70%RH.

Operational environment and operational conditions

This product is not chemical-proof or rust-proof.

In order to prevent this product from leakage of electricity and/or abnormal temperature increase, do not use the product under the following circumstances:

- (1) in an atmosphere containing corrosive gas (Cl₂, NH₃, SO₂, NO_x and so on).
- (2) in a dusty place.
- (3) in a place exposed to direct sunlight.
- (4) in such a place where water splashes or in such a humid place where water condenses.
- (5) in a place exposed to sea breeze.
- (6) in any other places similar to the above (1)through (5).

Operational Conditions

Please use the product within specified values (power supply, temperature, input, output and load condition etc.). Input voltage drops for line impedance, so please make sure that input voltage is within in specified values.

If the product is used over the specified values, it may damage the product, reduce the quality, and even if the products can endure the condition for short time, it may cause degradation of the reliability.

Note Prior to use

If you apply high static electricity, voltage higher than rated voltage or reverse voltage to the product, it may cause defects in the products or degrade the reliability.

Please avoid the following items:

1. Over rating power supply, reverse power supply or not-enough connection of input voltage and 0V(DC)line
2. Electrostatic discharge by production line and/or operator
3. Electrified product by electrostatic induction

Do not subject product to excessive mechanical shock. If you drop the product on the floor it might cause a crack to the core of inductors and monolithic ceramic capacitors.

Also please pay attention to handling; the mounted parts can be dislodged if subjected to excessive force.

Transportation

If you transport the product, please pack it so that the package will not be damaged by mechanical vibration or mechanical shock, and please educate and guide the carrier to prevent rough handling.

Revision History

VERSION	DATE	MODIFICATION	PAGE
A01	JUL-2025	New document	
A02	MAR-2026	Added MYBSP01201ABFS, MYBSP01201ABFT and MYBSP01201ABFU	

Notices

Scope

This datasheet is applied to MYBSP00502ABFS, MYBSP00502ABFT, MYBSP00502ABFU, MYBSP01201ABFS, MYBSP01201ABFT and MYBSP01201ABFU.

- Specific applications: Consumer Electronics, Industrial Equipment

CAUTION

Limitation of Applications

The products listed in the datasheet (hereinafter the product(s) is called the "Product(s)") are designed and manufactured for applications specified in the specification or the datasheet. (hereinafter called the "Specific Application"). We shall not warrant anything in connection with the Products including fitness, performance, adequateness, safety, or quality, in the case of applications listed in from (1) to (11) written at the end of this precautions, which may generally require high performance, function, quality, management of production or safety. Therefore, the Product shall be applied in compliance with the specific application.

We disclaim any loss and damages arising from or in connection with the products including but not limited to the case such loss and damages caused by the unexpected accident, in event that (i) the product is applied for the purpose which is not specified as the specific application for the product, and/or (ii) the product is applied for any following application purposes from (1) to (11) (except that such application purpose is unambiguously specified as specific application for the product in our catalog specification forms, datasheets, or other documents officially issued by us*).

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Power plant control equipment
- (5) Medical equipment
- (6) Transportation equipment (such as vehicles, trains, ships)
- (7) Traffic control equipment
- (8) Disaster prevention / crime prevention equipment
- (9) Industrial data-processing equipment
- (10) Combustion/explosion control equipment
- (11) Application of similar complexity and/or reliability requirements to the applications listed in the above

For exploring information of the Products which will be compatible with the particular purpose other than those specified in the datasheet, please contact our sales offices, distribution agents, or trading companies with which you make a deal, or via our web contact form.


Contact form: <https://www.murata.com/contactform>

*We may design and manufacture particular Products for applications listed in (1) to (11). Provided that, in such case we shall unambiguously specify such Specific Application in specification or datasheet without any exception. Therefore, any other documents and/or performances, whether exist or non-exist, shall not be deemed as the evidence to imply that we accept the applications listed in (1) to (11).

Fail-safe function

Be sure to add an appropriate fail-safe function to your finished product to prevent secondary damage in the unlikely event of an abnormality function or malfunction in our product.

Please connect the input terminal by right polarity. If you mistake the connection, it may break the DC-DC converter. In the case of destruction of the DC-DC converter inside, over input current may flow. Please add a diode and fuse as following to protect them.



Please select diode and fuse after confirming the operation.

⚠ Note

1. Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
2. You are requested not to use our product deviating from the reference specifications.
3. If you have any concerns about materials other than those listed in the RoHS directive, please contact us.
4. Please don't wash this product under any conditions.

Product Specification

Product Specification in this datasheet are as of March 2026. Specifications and features may change in any manner without notice. Please check with our sales representatives.

Contact form

<https://www.murata.com/contactform?Product=Power%20Device>

Disclaimers

The information described in this data sheet was carefully crafted for accuracy. However this product is based on the assumption that it will be used after thoroughly verifying and confirming the characteristics and system compatibility. Therefore, Murata is not responsible for any damages caused by errors in the description of the datasheet.

Murata constantly strives improve the quality and reliability of our products, but it is inevitable that semiconductor products will fail with a certain probability. Therefore regardless of whether the use conditions are within the range of this data sheet, Murata is not responsible for any damage caused by the failure of this product., (for example, secondary damage, compensation for accidents, punitive damage, loss of opportunity, and etc.) Also, regardless of whether Murata can foresee the events caused by the failure of our product, Murata has no obligations or responsibilities.

The buyer of this product and developer of systems incorporating this product must analyze, evaluate, and make judgements at their own risk in designing applications using this product. The buyer and the developer are responsible for verifying the safety of this product and the applications, and complying with all applicable laws, regulations, and other requirements.

Furthermore, the buyer and developer are responsible for predicting hazards and taking adequate safeguards against potential events at your own risk in order to prevent personal accidents, fire accidents, or other social damage. When using this product, perform thorough evaluation and verification of the safety design designed at your own risk for this product and the application.

Murata assumes that the buyer and developer have the expertise to verify all necessary issues for proper use of the product as described above and to take corrective action. Therefore, Murata has no liability arising out of the use of the product. The buyer and developer should take all necessary evaluations, verifications, corrective actions and etc., in your own responsibility and judgment.

This data sheet does not guarantee or grant any license to the information, including patents, copyrights, and other intellectual property rights, of the Murata or third parties. Regardless of whether the information described in this datasheet is express or implied, Murata does not take any responsibility or liability for any claims, damages, costs, losses, etc. relating to intellectual property rights or other rights from third parties due to the use of these information.

Patent Statement

Murata products are protected to under one or more of the U.S. patents.

Copyright and Trademark

©2026 Murata Manufacturing Co., Ltd. All rights reserved.



This product is subject to the following operating requirements and the Life and Safety Critical Application Sales Policy.

Refer to: <https://www.murata.com/products/power/requirements>

Murata Manufacturing Co., Ltd makes no representation that the use of its products in the circuits described herein, or the use of other technical information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not imply the granting of licenses to make, use, or sell equipment constructed in accordance therewith.